



Hexagon socket head cap screw UNC 1960 series ASME B18.3 Alloy steel ASTM A574 Plain #5-40X7/8

Article number	U07000.012.0087
Brand	-
UBB	500620894179
UNSPSC	31161605
EAN	8717077356825
PKG. of 100	Full Box Only

Technical Parameters

Diameter (inch)	#5
Driving features	Hexagon socket
Head shape	Cylindrical head
Length (L) (Inch - ft)	7/8
Material	Alloy steel
Material technical	ASTM A574
Thread direction	Right
TPI	40
Surface treatment	Plain
Thread	Unified National Coarse

Standards

ASME	B18.3
------	-------

Info	Marking in accordance with ASTM A574 with manufacturer's identification mark only. Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems. Warning: electroplating of these products may cause hydrogen
------	--

embrittlement. ft =
fully threaded

FABORY OF COURSE.

Technical Specification

A	0,205
H	0.125
J	3/32
L _T (min.)	0.75
Threads per inch	40

Technical Drawing

