



Hexagon socket head shoulder screw UNC ASME B18.3 Alloy steel Plain (5/8)3/4X1.1/4

Article number	U07111.075.0125
Brand	-
UBB	500624172382
UNSPSC	31161605
EAN	8715492895257
PKG. of 1	Full Box Only

Technical Parameters

Length	1.1/4 Inch
Driving features	Hexagon socket
Head shape	Cylindrical Knurled
Material	Alloy steel
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse

Info

All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread tolerance class for these screws is 3A, plating can cause thread fit problems.

Standards

ASME	B18.3
BS	2470

Technical Specification

A (max.)	1
D	0.75

Technical Drawing

D1	0.625
E	0.875
H (max.)	0.5
J	0.375
Threads per inch	11
D (min.)	0.746
D (max.)	0.748

