



## Hexagon socket head shoulder screw UNC ASME B18.3 Alloy steel Plain (5/8)3/4X2 Inch

Article number	U07111.075.0200
Brand	-
UBB	500624172614
UNSPSC	31161605
EAN	8715492895288
PKG. of 1	Full Box Only

### Technical Parameters

Length	2 Inch
Driving features	Hexagon socket
Head shape	Cylindrical Knurled
Material	Alloy steel
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse

Info

All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread tolerance class for these screws is 3A, plating can cause thread fit problems.

### Standards

BS	2470
ASME	B18.3

### Technical Specification

A (max.)	1
D	0.75

### Technical Drawing

D1	0.625
E	0.875
H (max.)	0.5
J	0.375
Threads per inch	11
D (min.)	0.746
D (max.)	0.748

