



**Hexagon socket  
countersunk head screw  
UNC ASME B18.3 Alloy steel  
ASTM F835 Plain #2-56X3/16  
ft**

Article number	U07410.008.0018
Brand	-
UBB	500621010221
UNSPSC	31161518
EAN	8717077365728
PKG. of 100	Full Box Only

**Technical Parameters**

Diameter	NO.2
Length	3/16 Inch
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse

**Standards**

ASME	B18.3
------	-------

Info

ft = fully threadedAll dimensions in above table are in inches.Marking of these screws is not mandatory.Due to the unfavourable head geometry these fasteners have reduced loadability.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can

**FABORY** cause thread fit problems.

**Technical Specification**

A	0.197
H	0.064
J	0.05
LT (min.)	0.62
Threads per inch	56

**Technical Drawing**

