



**Hexagon socket
countersunk head screw
UNC ASME B18.3 Alloy steel
ASTM F835 Plain 1.1/4-7X3
Inch ft**

Article number	U07410.125.0300
Brand	-
UBB	500621033587
UNSPSC	31161518
EAN	8717077368026
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.1/4 Inch
Length	3 Inch
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse

Standards

ASME	B18.3
------	-------

Info

ft = fully threadedAll dimensions in above table are in inches.Marking of these screws is not mandatory.Due to the unfavourable head geometry these fasteners have reduced loadability.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can

FABORY cause thread fit problems.

Technical Specification

A	2.438
H	0.683
J	0.875
LT (min.)	3.12
Threads per inch	7

Technical Drawing

