

Hexagon socket countersunk head screw UNC ASME B18.3 Alloy steel ASTM F835 Plain 1.1/4-7X3 Inch ft



Article number	U07410.125.0300
Brand	-
UBB	500621033587
UNSPSC	31161518
EAN	8717077368026
PKG. of 1	Full Box Only

Technical Parameters

Standards

Info	All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems.
------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

ASME B18.3

Diameter (inch)	1.1/4
Driving features	Hexagon socket
Head shape	Countersunk head
Length (L) (Inch - ft)	3 Inch
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
TPI	7
Surface treatment	Plain

Thread	Unified National Coarse
--------	----------------------------

Info **FABON** *OF COURSE* = fully threaded
SETTING THE STANDARD
IN FASTENING SOLUTIONS

Technical Specification

A	2.438
H	0.683
J	7/8
L _T (min.)	3.12
Threads per inch	7

Technical Drawing

