



**Hexagon socket  
countersunk head screw  
UNC ASME B18.3 Alloy  
steel ASTM F835 Zinc plated  
#4-40X3/8 ft**

Article number	U07415.011.0037
Brand	-
UBB	500621034320
UNSPSC	31161518
EAN	8717077368101
PKG. of 100	Full Box Only

**Technical Parameters**

Diameter	NO.4
Length	3/8 Inch
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse

**Standards**

ASME	B18.3
------	-------

Info  
ft = fully threadedAll dimensions in above table are in inches.Marking of these screws is not mandatory.Due to the unfavourable head geometry these fasteners have reduced loadability.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can

**FABORY** cause thread fit problems.

### Technical Specification

A	0.255
H	0.083
J	0.0625
LT (min.)	0.75
Threads per inch	40

### Technical Drawing

