



**Hexagon socket
countersunk head screw
UNC ASME B18.3 Alloy
steel ASTM F835 Zinc plated
#4-40X3/4 ft**

Article number	U07415.011.0075
Brand	-
UBB	500621034650
UNSPSC	31161518
EAN	8717077368132
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.4
Length	3/4 Inch
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse

Standards

ASME	B18.3
------	-------

Info
ft = fully threadedAll dimensions in above table are in inches.Marking of these screws is not mandatory.Due to the unfavourable head geometry these fasteners have reduced loadability.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can

FABORY cause thread fit problems.

Technical Specification

A	0.255
H	0.083
J	0.0625
LT (min.)	0.75
Threads per inch	40

Technical Drawing

