



## Hexagon socket countersunk head screw UNC ASME B18.3 Alloy steel ASTM F835 Zinc plated #4-40X1 Inch

Article number	U07415.011.0100
Brand	-
UBB	500621034734
UNSPSC	31161518
EAN	8717077368149
PKG. of 100	Full Box Only

### Technical Parameters

Info	All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems.
Diameter (inch)	#4
Driving features	Hexagon socket
Head shape	Countersunk head
Length (L) (Inch - ft)	1 Inch
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
TPI	40
Surface treatment	Zinc plated

### Standards

ASME	B18.3
------	-------

Thread Unified National  
Coarse

Info **FABON** *OF COURSE* = fully threaded  
SETTING THE STANDARD  
IN FASTENING SOLUTIONS

### Technical Specification

A	0.255
H	0.083
J	1/16
L <sub>T</sub> (min.)	0.75
Threads per inch	40

### Technical Drawing

