

Hexagon socket set screw with cup point UNC ASME B18.3 Alloy steel ASTM F912 Plain 3/4-10X2.1/2



Article number	U07840.075.0250
Brand	-
UBB	500624382759
UNSPSC	31161518
EAN	8717077373327
PKG. of 5	Full Box Only

Technical Parameters

Info	All dimensions in above table are in inches. These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.
Diameter (inch)	3/4
Driving features	Hexagon socket
Length (L) (Inch - ft)	2.1/2
Material	Alloy steel
Material technical	ASTM F912
Thread direction	Right
TPI	10
Surface treatment	Plain
Thread	Unified National Coarse

Standards

ASME	B18.3
BS	2470

Technical Specification

C (max.)	0.450
J	3/8
t (min.)	0.375
Threads per inch	10

Technical Drawing

