



**Machine screw truss slot
UNC asme B18.6.3 ASME
B18.6.3 Low carbon steel
Zinc plated #6-32X3/4**

Article number	U24861.013.0075
Brand	-
UBB	500624960836
UNSPSC	31161504
EAN	8712423001619
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.6
Length	3/4 Inch
Driving features	Slotted
Head shape	Truss head
Material	Low carbon steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse
Threads per inch	32

Info	Screws with diameter ≤ No.5 and length ≤ 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min.Screws with diameter No.5 and length ≤ 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.
------	---

Standards

ASME	B18.6.3
------	---------

Technical Specification

A (max.)	0.321
H (max.)	0.086

Technical Drawing

J (max.)	0.048
T (max.)	0.05

FABORY

