



Machine screw round head slot UNC asme B18.6.3 ASME B18.6.3 Brass #12-24X1 Inch

Article number	U48210.021.0100
Brand	-
UBB	500624974795
UNSPSC	31161504
EAN	8717077797512
PKG. of 50	Full Box Only

Technical Parameters

Diameter	NO.12
Length	1 Inch
Driving features	Slotted
Head shape	Round head
Material	Brass
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	24
Info	Screws with diameter \leq No.5 and length \leq 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length \leq 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

Standards

ASME	B18.6.3
------	---------

Technical Specification

A (max.)	0.408
H (max.)	0.153
J (max.)	0.067

Technical Drawing

T (max.) 0.096

FABORY

