



BLIC BOKW BRA-VPA 75G

Article No.	W2654.000.075
-------------	---------------

Brand	-
-------	---

UBB	500503227885
-----	--------------

UNSPSC	31162702
--------	----------

EAN	4047526274658
-----	---------------

PKG. of 1	Full Box Only
-----------	---------------

Technical Parameters

Bearing type	Plain bore
--------------	------------

Load capacity (kg)	60
--------------------	----

Plate size	43
------------	----

Wheel diameter (mm)	75
---------------------	----

With brake	No
------------	----

Info	<p>Casing: pressed steel, swivel castor casing with double ball bearing in the flange, bolted wheel axle, zinc plated and chromated.</p> <p>Wheels: VPA tyre: grey solid rubber, non-marking, 80° Shore A. Rims: high quality nylon with plain bearing, colour black. Additional remark for size description: G = plain bearing.</p>
------	--

Standards