



BLIC CASTOR/BR LKPA-VPA 126G-FI

Article No.	W2683.000.126
Brand	-
UBB	500503230913
UNSPSC	31162702
EAN	4047526225636
PKG. of 1	Full Box Only

Technical Parameters

Bearing type	Plain bore
Load capacity (kg)	120
Plate size	90 x 66
Wheel diameter (mm)	125
With brake	Yes

Info

Casing: pressed steel, swivel castor casing with double ball bearing in the flange, bolted wheel axle, zinc plated and chromated.
Wheels: VPA tyre: grey solid rubber, non-marking, 80° Shore A. Rims: high quality nylon with plain bearing, colour black. Additional remark for size description: G = plain bearing.

Standards