



BLIC CASTOR LE-VE 160R

Article No.	W2803.020.160
-------------	---------------

Brand	-
-------	---

UBB	500503174657
-----	--------------

UNSPSC	31162702
--------	----------

EAN	4047526277727
-----	---------------

PKG. of 1	Full Box Only
-----------	---------------

Technical Parameters

Bearing type	Roller bearing
--------------	----------------

Load capacity (kg)	135
--------------------	-----

Plate size	140 x 110
------------	-----------

Wheel diameter (mm)	160
---------------------	-----

With brake	No
------------	----

Info	Casing: pressed steel, swivel castor casing with double ball bearing in the flange, dynamically pressed using a special Blickle procedure giving little play on the flange and an extremely long lifespan, with stable central bolt, bolted wheel axle, zinc plated and chromated. Wheels: VE tyre: standard solid rubber, colour black, 80° Shore A. Rims: pressed steel, with roller bearing, zinc plated and chromated. Additional remark for
------	--

Standards

size description: R =
roller bearing.

FABORY *OF COURSE.*
SETTING THE STANDARD
IN FASTENING SOLUTIONS