



## BLIC CASTOR/BR LE-VE 100R-FI

Article No.	W2805.020.100
Brand	-
UBB	500503175647
UNSPSC	31162702
EAN	4047526281403
PKG. of 1	Full Box Only

### Technical Parameters

Bearing type	Roller bearing
Load capacity (kg)	70
Plate size	100 x 85
Wheel diameter (mm)	100
With brake	Yes

#### Info

Casing: pressed steel, swivel castor casing with double ball bearing in the flange, dynamically pressed using a special Blicke procedure giving little play on the flange and an extremely long lifespan, with stable central bolt, bolted wheel axle, zinc plated and chromated. Wheels: VE tyre: standard solid rubber, colour black, 80° Shore A. Rims: pressed steel, with roller bearing, zinc plated and chromated.  
Additional remark for

### Standards

size description: R =  
roller bearing.

**FABORY** *OF COURSE.*  
SETTING THE STANDARD  
IN FASTENING SOLUTIONS