



## BLIC CASTOR/BR L-VW 125R-FI

Article No.	W2904.020.125
Brand	-
UBB	500503182247
UNSPSC	31162702
EAN	4047526608637
PKG. of 1	Full Box Only

### Technical Parameters

Bearing type	Roller bearing
Load capacity (kg)	50
Plate size	100 x 85
Wheel diameter (mm)	125
With brake	Yes

#### Info

Casing: pressed steel, swivel castor casing with double ball bearing in the flange, dynamically pressed using a special Blicke procedure giving little play on the flange and an extremely long lifespan, with stable central bolt, with flange seal, bolted wheel axle, zinc plated and chromated. Wheels: VW tyre: soft rubber Blicke®soft, colour black, 50° Shore A, very low noise. Rims: pressed steel, with steel hub bush, with roller

### Standards

**FABORY**

SETTING THE STANDARD  
IN FASTENING SOLUTIONS

**OF COURSE.**

bearing, zinc plated  
and chromated.

This special Blicke  
rim construction  
is extraordinarily  
stable, even under  
the duress of shock  
or impact and has  
an elegant design  
into the bargain.

Additional remark for  
size description: R =  
roller bearing.