



BLIC CASTOR L-VWPP 125G

Article number	W2911.000.125
----------------	---------------

Brand	-
-------	---

UBB	500503186123
-----	--------------

UNSPSC	31162702
--------	----------

EAN	4047526578152
-----	---------------

PKG. of 1	Full Box Only
-----------	---------------

Technical Parameters

Type	Zwenkwiel
Bearing type	Plain bore
Load capacity (kg)	50
Plate size	100 x 85
Wheel diameter (mm)	125
With brake	No

Standards

Info	Casing: pressed steel, swivel castor casing with double ball bearing in the flange, dynamically pressed using a special Blicke procedure giving little play on the flange and an extremely long lifespan, with stable central bolt, with flange seal, bolted wheel axle, zinc plated and chromated. Wheels: VWPP tyre: soft rubber Blicke@soft, colour black, 50° Shore A, very low noise. Rims:
------	--

polypropylene,
shock and impact
resistant, corrosion-
resistant, with plain
bearing, colour
black. Additional
remark for size
description: G = plain
bearing.