



BLICK CASTOR L-POEV 200R

Article No.	W2953.020.200
-------------	---------------

Brand	-
-------	---

UBB	500503180670
-----	--------------

UNSPSC	31162702
--------	----------

EAN	4047526043070
-----	---------------

PKG. of 1	Full Box Only
-----------	---------------

Technical Parameters

Bearing type	Roller bearing
--------------	----------------

Load capacity (kg)	400
--------------------	-----

Plate size	140 x 110
------------	-----------

Wheel diameter (mm)	200
---------------------	-----

With brake	No
------------	----

Info	Casing: pressed steel, swivel castor casing with double ball bearing in the strengthened flange, dynamically pressed using a special Blickle procedure giving little play on the flange and an extremely long lifespan, with stable central bolt (wheel- \varnothing 160-250mm), with flange seal, bolted wheel axle, zinc plated and chromated. Wheels: POEV tyre: elastic solid rubber, smooth running qualities, colour black, 65° Shore A, vulcanised,
------	--

Standards

unbreakable joint,
minimal rolling
friction. Rims: high
quality nylon, colour
black, shock and
impact resistant,
corrosion-resistant,
with roller or ball
bearing. Additional
remark for size
description: R =
roller bearing. K =
ball bearing.