



BLIC CASTOR L-POTH 150R

Article No.	W3221.020.150
-------------	---------------

Brand	-
-------	---

UBB	500503181173
-----	--------------

UNSPSC	31162702
--------	----------

EAN	4047526044558
-----	---------------

PKG. of 1	Full Box Only
-----------	---------------

Technical Parameters

Bearing type	Roller bearing
--------------	----------------

Load capacity (kg)	400
--------------------	-----

Plate size	140 x 110
------------	-----------

Wheel diameter (mm)	150
---------------------	-----

With brake	No
------------	----

Info	Casing: pressed steel, swivel castor casing with double ball bearing in the strengthened flange, dynamically pressed using a special Blickle procedure giving little play on the flange and an extremely long lifespan, with stable central bolt (wheel- \varnothing 150+200mm), with flange seal, bolted wheel axle, zinc plated and chromated. Wheels: POTH tread: polyurethane, injection-moulded, colour brown, non-marking, 98°
------	--

Standards

Shore A, wear-resistant, no surface discoloration, spares the floor, low noise, minimal rolling friction, keeps its shape and chemical bonding to the rim.

Rims: high quality nylon, colour off-white, shock and impact resistant, corrosion-resistant, with roller bearing.

Additional remark for size description: R = roller bearing.