



BLICK CASTOR L-ALST 200K

Article No.	W3251.010.200
-------------	---------------

Brand	-
-------	---

UBB	500511059015
-----	--------------

UNSPSC	31162702
--------	----------

EAN	4047526579401
-----	---------------

PKG. of 1	Full Box Only
-----------	---------------

Technical Parameters

Bearing type	Ball bearing
--------------	--------------

Load capacity (kg)	400
--------------------	-----

Plate size	140 x 110
------------	-----------

Wheel diameter (mm)	200
---------------------	-----

With brake	No
------------	----

Info	Casing: pressed steel, swivel castor casing with double ball bearing in the strengthened flange, dynamically pressed using a special Blickle procedure giving little play on the flange and an extremely long lifespan, with stable central bolt (wheel- \varnothing 160+200mm), with flange seal, bolted wheel axle, zinc plated and chromated. Wheels: ALST tread: Blickle Softhane®, die cast, colour green, non-marking, very good rolling characteristics
------	--

Standards

FABORY

SETTING THE STANDARD
IN FASTENING SOLUTIONS

OF COURSE.

due to particularly wide, elastic tread, 75° Shore A, elastic, wear-resistant, highly resistant to notches and grooves, no surface discolouration, spares the floor, low noise, minimal rolling resistance, very good chemical bonding to the rim. Rims: cast aluminium, corrosion-resistant, with ball bearing. Additional remark for size description: K = ball bearing.