



## BLIC CASTOR LE-PO 75R

Article number	W3403.020.075
----------------	---------------

Brand	-
-------	---

UBB	500504113753
-----	--------------

UNSPSC	31162702
--------	----------

EAN	4047526334048
-----	---------------

PKG. of 1	Full Box Only
-----------	---------------

### Technical Parameters

Type	Zwenkwiel
Bearing type	Roller bearing
Load capacity (kg)	150
Plate size	100 x 85
Wheel diameter (mm)	75
With brake	No

### Standards

Info	Casing: pressed steel, swivel castor casing with double ball bearing in the flange, dynamically pressed using a special Blicke procedure giving little play on the flange and an extremely long lifespan, with stable central bolt, bolted wheel axle, zinc plated and chromated. Wheels: PO: high quality nylon, colour off-white, high wear resistance, minimal rolling friction, runs well on smooth
------	---

floors, shock and impact resistant, corrosion-resistant, high chemical resistance to alcohol, salt, fats and certain acids and caustic solutions in diluted concentrate, with roller or ball bearing. Additional remark for size description: G = plain bearing. R = roller bearing. K = ball bearing.