



BLIC CASTOR LE-PO 75R

Article No.	W3403.020.075
-------------	---------------

Brand	-
-------	---

UBB	500504113753
-----	--------------

UNSPSC	31162702
--------	----------

EAN	4047526334048
-----	---------------

PKG. of 1	Full Box Only
-----------	---------------

Technical Parameters

Bearing type	Roller bearing
--------------	----------------

Load capacity (kg)	150
--------------------	-----

Plate size	100 x 85
------------	----------

Wheel diameter (mm)	75
---------------------	----

With brake	No
------------	----

Info	Casing: pressed steel, swivel castor casing with double ball bearing in the flange, dynamically pressed using a special Blicle procedure giving little play on the flange and an extremely long lifespan, with stable central bolt, bolted wheel axle, zinc plated and chromated. Wheels: PO: high quality nylon, colour off-white, high wear resistance, minimal rolling friction, runs well on smooth floors, shock and impact resistant,
------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Standards

corrosion-resistant,
high chemical
resistance to alcohol,
salt, fats and certain
acids and caustic
solutions in diluted
concentrate, with
roller or ball bearing.
Additional remark for
size description: G
= plain bearing. R =
roller bearing. K =
ball bearing.