



Hexagon head bolt DIN 931 Steel Zinc plated 8.8 M14X65/S=22

Article number	01200.140.065
Brand	-
UBB	950351150541
UNSPSC	31161620
EAN	8715492026279
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	65 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	1555
ASME	B18.2.3.1M
NF	E25-112
ISO	4014
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	65
P	2
s	22

Technical Drawing

