



Slotted cheese head screw DIN 84 Stainless steel A2 70 M4X12

Article number	51120.040.012
Brand	-
UBB	950353259506
UNSPSC	31161504
EAN	8715492271426
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	12 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	84
ASME	≈B18.6.7M
NF	≈E25-127
BS	≈4183
NEN	≈1602
ISO	≈1207

Technical Specification

d-D	M4
Thread length (min.)	38
dk (max.)	7
Full thread if L ≤	40
k (max.)	2.6
L (mm)	12
n	1.2
P	0.7
t (min.)	1.1

Technical Drawing