



M10 S/20

Artículo No.	90251FIS
Marca	-
UBB	500616785589
UNSPSC	31161607
EAN	4006209902516
Env. de 1	Solo embalaje completo

Parámetros técnicos

Diámetro	10 mm
Longitud	90 mm
Características clave	Functioning - The TAM is suitable for pre-positioned installation. - When applying the torque, the cone is pulled into the expansion sleeve and expands it against the drill hole wall. - For correct installation, it must be ensured that the pre-positioned anchor TAM can be supported on the attachment, or that the threaded rod is countered. - Determining the screw length l_s : $Screw\ length\ l_s = Length\ of\ fixing + Thickness\ of\ fixture\ t_{fix} + Thickness\ of\ washer.$
Aprobación de ETA	Yes
Info	do= Nominal diameter of drill bit.dd= Embedment depth.df= Anchor diameter.fs= Head

Normas

diameter.Ws=
Setting tool
diameter.hef=
Effective anchorage
depth.tfix= Grip
range.kN =
Allowable load in kN.

Especificación técnica

Diseño técnico

