

M12X180



Artículo No.	90285FIS
Marca	-
UBB	500616696315
UNSPSC	31161601
EAN	4006209902851
Env. de 1	Solo embalaje completo

Parámetros técnicos

Diámetro	M12
Longitud	180 mm
Aprobación de ETA	Yes

Info

Ccr, N =
Characteristic
Edge distance
(tensile).Cmin. =
Minimum edge
distance (tensile).df
= Hole diameter
in fixture.do =
Hole diameter in
substrate.hef =
Effective embedment
depth.hmin =
Minimum substrate
thickness.ho =
Minimum hole
depth.Scr, N =
Characteristic
spacing.Concrete
C20/25
recommended load
for non-cracked
concrete.The
allowable load is only
valid for AcryMaxx
Chemical Mortar
in combination
with Anchor studs,
steel grade 5.8.The
allowable load is
valid for one single

Normas

FABORY

anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the S_{cr} , N and C_{cr} , N are taken in to account. Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Especificación técnica

Diseño técnico

