



Anclaje perno 12/120

Artículo No.	96367FIS
Marca	-
UBB	500616705975
UNSPSC	31162101
EAN	4006209963678
Env. de 1	Solo embalaje completo

Parámetros técnicos

Diámetro	M12
Longitud	151 mm
Características clave	<p>Functioning - The FAZ II is suitable for pre-positioned and push-through installation; also suitable for stand-off installation under certain conditions. - Prior to installation, place the hexagon nut in the optimal position (the drive-in pin projects by approx. 3 mm out of the hexagon nut). - When applying the torque, the cone bolt is pulled into the expansion clip and expands it against the drill hole wall. - The head embossing offers a simple control of the anchoring. - In the case of series installation, we recommend using the FABS bolt anchor setting tool.</p>

Normas

Info

FABORY

do= Nominal diameter of drill bit.Min. td= Recommended drilling depth.hef= Effective anchorage depth.tfix= Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the Scr, N and Ccr, N are taken in to account.Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Especificación técnica

Diseño técnico

