



Anclaje perno tipo FH II-B M16X160/60

Artículo No.	97627FIS
Marca	-
UBB	500616710660
UNSPSC	31162101
EAN	4006209976272
Env. de 1	Solo embalaje completo

Parámetros técnicos

Diámetro	M16
Info	do= Nominal diameter of drill bit.Min. td= Recommended drilling depth.hef= Effective anchorage depth.tfix= Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the S_{cr}, N and C_{cr}, N are taken in to account.When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request.Final calculations should

Normas

FABORY

comply with the
complete European
Technical Approval
(ETA), this approval
is also available on
request.

Especificación técnica

Diseño técnico

