

6/5 (6X50)



Artículo No.	97729FIS
Marca	-
UBB	500616934823
UNSPSC	31162101
EAN	
Env. de 1	Solo embalaje completo

Parámetros técnicos

Diámetro	M8
Longitud	17 mm
Info	<p>do = Nominal diameter of drill bit. Min. td = Advised drilling depth. hef = Effective anchorage depth. tfix = Grip range. kN = Recommended load in kN. The allowable load is valid for 1 separate anchor, for cracked concrete (tensile zone) in the class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and when the Scr, N and Ccr, N are not exceeded. For the final calculations, it is mandatory to take into account the entire European Technical Approval (ETA), which is available on request. ETA option only for M8-M20</p>

Normas

Especificación técnica

d-D

M8

Diseño técnico

do	6
Agujero ø	6
hef	29
L (mm)	17
Min. td	50
Largura del taco	50
s	10
tfix	5

