



Goujon d'ancrage 12/30

Numéro d'article	96340FIS
Marque	-
UBB	500616705892
UNSPSC	31162101
EAN	4006209963401
PKG. de 20	Boîte complete uniquement

Paramètres techniques

Diamètre	M12
Longueur	81 mm
Principales caractéristiques	<p>Functioning - The FAZ II is suitable for pre-positioned and push-through installation; also suitable for stand-off installation under certain conditions. - Prior to installation, place the hexagon nut in the optimal position (the drive-in pin projects by approx. 3 mm out of the hexagon nut). - When applying the torque, the cone bolt is pulled into the expansion clip and expands it against the drill hole wall. - The head embossing offers a simple control of the anchoring. - In the case of series installation, we recommend using the FABS bolt anchor setting tool.</p>

Normes

Info

FABORY

do= Nominal diameter of drill bit. Min. td= Recommended drilling depth. hef= Effective anchorage depth. tfix= Grip range. s = Width across flats. kN = Load in kN. The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the Scr, N and Ccr, N are taken in to account. Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Spécifications techniques

Dessin technique

