

## Cheville haute performance type FH II-B M8X60/50



Numéro d'article	97034FIS
Marque	-
UBB	500616707385
UNSPSC	31162101
EAN	4006209970348
PKG. de 10	Boîte complete uniquement

### Paramètres techniques

Diamètre	M8
----------	----

#### Info

do= Nominal diameter of drill bit.Min. td= Recommended drilling depth.hef= Effective anchorage depth.tfix= Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor  $\gamma_f = 1,4$  and if the  $S_{cr}$ , N and  $C_{cr}$ , N are taken in to account.When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request.Final calculations should

### Normes

# FABORY

comply with the  
complete European  
Technical Approval  
(ETA), this approval  
is also available on  
request.

## Spécifications techniques

## Dessin technique

