



Cheville haute performance type FH II-B M10X60/20

Numéro d'article	97073FIS
Marque	-
UBB	500616707955
UNSPSC	31162101
EAN	4006209970737
PKG. de 10	Boîte complete uniquement

Paramètres techniques

Diamètre	M10
Info	<p>do= Nominal diameter of drill bit.Min. td= Recommended drilling depth.hef= Effective anchorage depth.tfix= Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the S_{cr}, N and C_{cr}, N are taken in to account.When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request.Final calculations should</p>

Normes

FABORY

comply with the
complete European
Technical Approval
(ETA), this approval
is also available on
request.

Spécifications techniques

Dessin technique

