



Cheville haute performance type FH II-B M10X95/20

Numéro d'article	97617FIS
Marque	-
UBB	500616709696
UNSPSC	31162101
EAN	4006209976173
PKG. de 10	Boîte complete uniquement

Paramètres techniques

Diamètre	M10
----------	-----

Info

do= Nominal diameter of drill bit.Min. td= Recommended drilling depth.hef= Effective anchorage depth.tfix= Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the S_{cr} , N and C_{cr} , N are taken in to account.When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request.Final calculations should

Normes

FABORY comply with the
complete European
Technical Approval
(ETA), this approval
is also available on
request.

Spécifications techniques

Dessin technique

