



6/5 (6X50)

Numéro d'article	97729FIS
Marque	-
UBB	500616934823
UNSPSC	31162101
EAN	
PKG. de 1	Boîte complete uniquement

Paramètres techniques

Diamètre	M8
Longueur	17 mm
Info	do = Nominal diameter of drill bit.Min. td = Advised drilling depth.hef = Effective anchorage depth.tfix = Grip range.kN = Recommended load in kN.The allowable load is valid for 1 separate anchor, for cracked concrete (tensile zone) in the class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and when the Scr, N and Ccr, N are not exceeded.For the final calculations, it is mandatory to take into account the entire European Technical Approval (ETA), which is available on request.ETA option only for M8-M20

Normes

Spécifications techniques

d-D	M8
-----	----

Dessin technique

do	6
Foret ø	6
hef	29
L (mm)	17
Min. td	50
Long. de la cheville	50
s	10
tfix	5

