



## KNIP OLDALCSÍPŐ. 74 7421-200MM

Cikkszám	K1074.120.200
Márka	-
UBB	419104300365
UNSPSC	23151901
EAN	4003773050483
csom. 1	Csak bontatlan csomagban

### Műszaki adatok

Kapacitás	3
Egész hosszúság	200
Verzió	Krómozott & műanyaggal bevonva

### Megjegyzések

With forged-on axle for heaviest duty. Vanadium electric steel, oil-hardened and tempered  
Vanadium electric steel, oil-hardened and tempered.  
Model 74 21 200/74 22 200: Style 2: 12° angled head for flush cutting, providing space of approximately 70mm for gripping. Style 9: centre cutter.  
Finish 1 = Head polished. Handles plastic coated.  
Finish 2 = Head polished. Handles with two-colour dual component sleeves. Finish 4 = Plier chrome plated. Finish 5 = Plier chrome

### Szabványok

ISO	5749
-----	------

plated. Handles  
with two-colour  
dual component  
sleeves. Finish 6 =  
Plier chrome plated.  
Handles insulated  
with two-colour dual  
component sleeves  
1000 V VDE-tested  
DIN EN/IEC 60900.  
Finish 7 = Plier  
chrome plated.  
Handles dipped  
plastic insulated  
1000 V VDE-tested  
DIN EN/IEC 60900.