



## KNIP OLDALCSÍPŐ. 74 7406-180MM

Cikkszám	K1074.600.180
Márka	-
UBB	419104212339
UNSPSC	23151901
EAN	4003773022985
csom. 1	Csak bontatlan csomagban

### Műszaki adatok

Kapacitás	2.7
Egész hosszúság	180
Verzió	Krómozott & többkomponensű burkolattal szigetelt, vde-típusengedély

Megjegyzések

With forged-on axle for heaviest duty. Vanadium electric steel, oil-hardened and tempered Vanadium electric steel, oil-hardened and tempered. Model 74 21 200/74 22 200: Style 2: 12° angled head for flush cutting, providing space of approximately 70mm for gripping. Style 9: centre cutter. Finish 1 = Head polished. Handles plastic coated. Finish 2 = Head polished. Handles with two-colour dual component sleeves. Finish 4 = Plier chrome plated. Finish 5

### Szabványok

ISO	5749
-----	------

**FABORY**

SETTING THE STANDARD  
IN FASTENING SOLUTIONS

**OF COURSE.**

= Plier chrome plated. Handles with two-colour dual component sleeves. Finish 6 = Plier chrome plated. Handles insulated with two-colour dual component sleeves 1000 V VDE-tested DIN EN/IEC 60900. Finish 7 = Plier chrome plated. Handles dipped plastic insulated 1000 V VDE-tested DIN EN/IEC 60900.