



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc plated 90 M6X30

Numero articolo	01049.060.030
Marchio	-
UBB	500577289530
UNSPSC	31161620
EAN	8715494322645
PKG. di 500	Solo full box

Parametri tecnici:

Diametro	M6
Lunghezza	30 mm
Class	90
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standard

DIN ≈6921

Specifica tecnica

d-D	M6
dc	14.2
k	5.5
L (mm)	30
P	1
s	10

Disegno tecnico

