

Small hexagon head set screw with undercut and full dog point DIN 561 Ri Steel Plain 22H M20X120



Numero articolo 01090.200.120

Marchio -

UBB 500647908226

UNSPSC 31161620

EAN 8717077270381

PKG. di 10 Solo full box

Parametri tecnici:

Diametro	M20
Lunghezza	120 mm
Threaded pitch (P)	2.5
Class	22H
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standard

DIN 561-Ri

Specifica tecnica

d-D	M20
dg	16.4
dp (max.)	15
g2	8.7
k	14
L (mm)	120
P	2.5
s	24
z2 (min.)	10

Disegno tecnico

