

Hexagon head bolt DIN 931 Steel Plain 10.9 M20X120

Numero articolo 04100.200.120

Marchio -

UBB 950351328360

UNSPSC 31161620

EAN 8715492115362

PKG. di 25 Solo full box

Parametri tecnici:

Diametro	M20
Lunghezza	120 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standard

NF	E25-112
ISO	4014
ASME	B18.2.3.1M
NEN	1555
DIN	931

Specifica tecnica

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	120
P	2.5
s	30

Disegno tecnico

