

## Hexagon nut ISO-Metric thread ISO 4032 Steel Hot dip galvanized 10 ISO metric M33

|                 |               |
|-----------------|---------------|
| Numero articolo | 04128.330.001 |
| Marchio         | -             |
| UBB             | 500648941788  |
| UNSPSC          | 31161727      |
| EAN             | 8717077238305 |
| PKG. di 10      | Solo full box |

### Parametri tecnici:

|                   |                    |
|-------------------|--------------------|
| Diametro          | M33                |
| Class             | 10                 |
| Driving features  | Hexagon            |
| Material          | Steel              |
| Thread direction  | Right              |
| Surface treatment | Hot dip galvanized |
| Thread            | Metric thread      |

### Standard

ISO 4032

Info ISO metric hot dip galvanized nuts are manufactured with thread tolerance class 6H and mate with externally threaded parts (bolts, threaded rods) that are manufactured with thread tolerance class 6az before coating. As the nut thread is tapped after galvanizing the threads are not coated. The corrosion resistance however is not influenced disadvantageously

as the thread will be  
protected by the zinc  
layer of the mating  
part.ISO metric

## Specifica tecnica

|          |      |
|----------|------|
| d-D      | M33  |
| m (max.) | 28.7 |
| P        | 3.5  |
| s        | 50   |

## Disegno tecnico

