



Hexagon socket head cap screw DIN 912 Steel Plain 12.9 M18X70

Numero articolo	07000.180.070
Marchio	-
UBB	950351383795
UNSPSC	31161605
EAN	8715492046727
PKG. di 25	Solo full box

Parametri tecnici:

Diametro	M18
Lunghezza	70 mm
Class	12.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standard

ISO	4762
DIN	912
NEN	1241
ASME	B18.3.1M
NF	E25-125
BS	4168-1

Specifica tecnica

b	48
d-D	M18
dk (max.)	27
Full thread if $L \leq$	65
k (max.)	18
L (mm)	70
P	2.5
s	14

Disegno tecnico

