



Hexagon socket head cap screw with low head and pilot recess DIN 6912 Steel Plain 08.8 M6X20

Numero articolo 07030.060.020

Marchio -

UBB 950351398728

UNSPSC 31161605

EAN 8715492053152

PKG. di 200 Solo full box

Parametri tecnici:

Diametro	M6
Lunghezza	20 mm
Class	08.8
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070',

Standard

DIN 6912

FABORY or with the steel
grade only, e.g. 'A2'.

Specifica tecnica

b (min.): $L \leq 125\text{mm}$	18
d-D	M6
dh	3
dk	10
Full thread if $L \leq$	25
k	4
L (mm)	20
P	1
s	5

Disegno tecnico

