



Hexagon socket head cap screw with low head DIN 7984 Steel Plain 010.9 M12X60

Numero articolo 07105.120.060

Marchio -

UBB 953351832084

UNSPSC 31161605

EAN 8715492064370

PKG. di 100 Solo full box

Parametri tecnici:

Diametro	M12
Lunghezza	60 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Warning:
electroplating of these products may cause hydrogen embrittlement. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked

Standard

DIN 7984

FABORY with a '0' preceding
the property class
mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Specifica tecnica

b (min.)	30
d-D	M12
dk	18
Full thread if $L \leq$	45
k	7
L (mm)	60
P	1.75
s	8

Disegno tecnico

