



## Hexagon socket countersunk head screw ISO 10642 Steel Zinc flake Cr(VI) free - flZn/nc 010.9 M10X50

Numero articolo 07407.100.050

Marchio -

UBB 500571181899

UNSPSC 31161518

EAN 8715494140232

PKG. di 100 Solo full box

### Parametri tecnici:

|                   |                                     |
|-------------------|-------------------------------------|
| Diametro          | M10                                 |
| Lunghezza         | 50 mm                               |
| Class             | 010.9                               |
| Driving features  | Hexagon socket                      |
| Head shape        | Countersunk head                    |
| Material          | Steel                               |
| Thread direction  | Right                               |
| Surface treatment | Zinc flake Cr(VI) free<br>- flZn/nc |
| Thread            | Metric thread                       |

### Info

A zinc flake coating eliminates the risk of hydrogen embrittlement. All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark,

### Standard

|     |       |
|-----|-------|
| DIN | ≈7991 |
| ISO | 10642 |

# FABORY

e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

## Specifica tecnica

|                         |       |
|-------------------------|-------|
| b (min.)                | 32    |
| d-D                     | M10   |
| dk (max.)               | 20.69 |
| Full thread if $L \leq$ | 50    |
| k (max.)                | 6.2   |
| L (mm)                  | 50    |
| P                       | 1.5   |
| s                       | 6     |
| $\alpha$                | 90    |

## Disegno tecnico

