



Hexalobular socket countersunk head screw ISO ≈10642 Steel Zinc plated 08.8 M4X8

Numero articolo	07450.040.008
-----------------	---------------

Marchio	-
---------	---

UBB	500645109496
-----	--------------

UNSPSC	31161518
--------	----------

EAN	8717077060821
-----	---------------

PKG. di 500	Solo full box
-------------	---------------

Parametri tecnici:

Diametro	M4
Lunghezza	8 mm
Class	08.8
Driving features	Hexalobular
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standard

ISO	≈10642
DIN	≈7991

Info

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070',

FABORY or with the steel
grade only, e.g. 'A2'.

Specifica tecnica

b (min.)	14
d-D	M4
dk	8
k (max.)	2.3
L (mm)	8
P	0.7
Socket	20
α	90

Disegno tecnico

