

Hexagon head bolt for pressure vessels ISO 4014 Steel (AD-W7) Plain 5.6 M24X110

Numero articolo	08750.240.110
Marchio	-
UBB	950351671132
UNSPSC	31161620
EAN	8715492564054
PKG. di 10	Solo full box

Parametri tecnici:

Diametro	M24
Lunghezza	110 mm
Class	5.6
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel (AD-W7)
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10 °C up to +300 °C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a

Standard

NEN	1555
DIN	931
ASME	B18.2.3.1M
NF	E25-112
ISO	4014

FABORY

certificate EN 10204
3.1 by marking
the fasteners
with the property
class and the
manufacturer's mark.
This recognition is
equally accepted
by Lloyd's Register
Energy for pressure
vessels

Specifica tecnica

b (min.): 125mm $L \leq 200$ mm	60
------------------------------------	----

b (min.): $L > 200$ mm	73
------------------------	----

b (min.): $L \leq 125$ mm	54
---------------------------	----

d-D	M24
-----	-----

k	15
---	----

L (mm)	110
--------	-----

P	3
---	---

s	36
---	----

Disegno tecnico

