



Prevailing torque type hexagon nut with non-metallic insert DIN 985 Steel Zinc plated yellow passivated |10| M20

Article number	12450.200.001
Brand	-
UBB	950355360518
UNSPSC	31161727
EAN	8715492578754
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Class	10
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	985
ISO	≈10511
NF	E25-412

Technical Specification

d-D	M20
h	20
P	2.5
s	30

Technical Drawing

