



Prevailing torque type hexagon nut with flange with non-metallic insert DIN 6926 Steel Zinc plated 8 M5

Article number	12460.050.001
Brand	-
UBB	950355958428
UNSPSC	31161727
EAN	8715492578792
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M5
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	6926
ISO	7043

Technical Specification

d-D	M5
dc (max.)	11.8
h (max.)	7.1
P	0.8
s	8

Technical Drawing

