



Slotted set screw with cone point DIN 553 Steel Plain 14H M10X50

Numero articolo 20030.100.050

Marchio -

UBB 950351719584

UNSPSC 31161505

EAN 8715492603203

PKG. di 100 Solo full box

Parametri tecnici:

Diametro	M10
Lunghezza	50 mm
Class	14H
Driving features	Slotted
Material	Steel
Thread direction	Right
Point	Cone
Surface treatment	Plain
Thread	Metric thread

Standard

ISO	7434
DIN	553
BS	4219
NEN	1488
NF	E25-161

Specifica tecnica

d-D	M10
dt (max.)	2.5
L (mm)	50
n	1.6
P	1.5

Disegno tecnico

